


Product	Nursing bench 2000, electrically height adjustable	
Item number	<p>R8468000  VVS: 777544280  EAN: 5708590315492  NBS: N13:40,375</p>	
Colour	White	
Description	<p>1800 mm powered nursing bench with wired hand control, 700 mm height adjustable. Incl. water collection tray with integrated outlet. Materials: Coated steel, mesh cover, polystyrene</p>	
Adjustability	Height adjustable	
Adjustment height	700 mm	
Maximum load	Maximum load: 175 kg	
Speed without load	Speed up: 15 mm/s Speed down: 20 mm/s	
Noise level	48 dB	
Material	<p>The frame is made from powder-laquered stainless steel, the lying surface is a mesh cover. The water collection tray is made from polystyrene.</p>	
Ergonomy	<p>Pressalit Care offers a range of high quality, fixed or power adjusted nursing benches designed to provide a stable platform suitable for changing adults and children in a variety of settings: schools, day care centres, institutions, hospitals and private homes. The nursing bench 3000 series provides for maximum safety and comfort. Besides an award winning design, the series includes comfortable and durable surfaces, including polyurethane foam and aluminum.</p> <p>The flexibility of the nursing bench provides for optimal working conditions for the carer as well as a high level of comfort and safety for the user.</p>	



Product	Nursing bench 2000, electrically height adjustable
<p>Features</p> <p>Mains connection (V)</p> <p>Actuator (motor)</p> <p>Control box</p> <p>Hand control</p> <p>Power usage</p>	<p>A water collection tray with integrated water outlet prevents water from splashing on carers or the floor. The flexible hose attached to the centre mounted outlet of the water collection tray, can be connected to either an outlet in the floor or on the wall. The integrated gas cylinders enable the bench to be folded out of the way when not in use to maximise floor space in front of the unit. Electric with wired hand control – the red buttons clearly indicate “Up” and “Down”. The wired hand control comes with a holder for fitting to the wall. The stretcher of the bench is very easy to clean, and the stretcher cover can be unzipped for washing or easy replacement.</p> <p>230</p> <p>LA31 Careline, (Linak), 6000 N, IPX6</p> <p>CB9 Careline, (Linak), IPX6</p> <p>HB7 (Linak), IP66</p> <p>Power consumption by maximum load: 70 W Power consumption by standby: 2 W</p>
Cleaning	<p>Pressalit Care recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.</p> <p>This product complies with the requirements of Council Directive 93/42/EEC concerning medical devices, as last amended by Council Directive 2007/47/EC of 5 September 2007. It also complies with all relevant requirements in the Council Directive 2006/42/EC (of 17 May 2006) on machinery.</p>

